

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201080248](#)
Status: **Active**
Overview: Brad® Industrial Ethernet Solutions
Description: Micro-Change® (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 22 AWG, Shielded PUR Cable, 20.0m (65.62') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change® (M12)
Connector End B	Micro-Change® (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad® Industrial Ethernet Solutions
Performance Category	5e
Product Name	Micro-Change® (M12)
Protocol	EtherNet
Region	America, Asia, Europe
Type	Double Ended
UPC	78172536921

Physical

Cable Diameter	6.70mm (.264")
Cable Length	20.0m (65.62')
Color - Cable Jacket	Green
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +60°C
Wire Size AWG	22
Wire/Cable Type	Shielded PUR

Electrical


Current - Maximum per Contact	1.5A
Voltage - Maximum	30V

Material Info

Engineering Number	E11A06011M200
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-120108-041, SD-120108-051
---------------	------------------------------



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per
-ED/01/2017 (12
January 2017)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120108](#) Series