

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [120086-0423](#)
Status: **Active**
Overview: [Brad® Nano-Change® (M8) Products](#)
Description: Nano-Change® (M8) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, with PNP LED Sensors, 24 AWG, PVC Cable, 5.0m (16.40') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [120086](#)
 Connector End A Nano-Change® (M8)
 Connector End B Pigtail
 IP Rating IP68
 Overview [Brad® Nano-Change® (M8) Products](#)
 Product Name Nano-Change® (M8)
 Protocol N/A
 Region America
 Type Single Ended
 UPC 78678833550

Physical

Cable Diameter 4.32mm (.170")
 Cable Length 5.0m (16.40')
 Color - Cable Jacket Yellow
 Coupling Style Threaded
 Gender Female-Pigtail
 LED Indicator For PNP Sensors
 Material - Cable Jacket PVC
 Material - Connector Body PVC
 Material - Contact Copper Alloy
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Viton
 Material - Plating Mating Gold over Nickel
 Orientation 90° to Straight
 Poles 3
 Temperature Range - Operating -20°C to +105°C
 Wire Size AWG 24
 Wire/Cable Type E152210

Electrical

Current - Maximum per Contact 3.0A
 Voltage - Maximum 30V AC/DC

Material Info

Old Part Number 4030P1A10M050

Reference - Drawing Numbers

Sales Drawing SD-120086-029



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Not Reviewed**
**Low-Halogen Status
 Not Reviewed**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[120086Series](#)

This document was generated on 04/17/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION