

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301280152

Status:

Active

Overview:

Watertite® Wet-Location Wiring Solutions

Description:

Watertite® Three-Gang FD PVC, Non-metallic Box, Yellow, 88.9mm (3.50") Depth, 109.1 Cubic Inch Capacity, 1" unthreaded conduit openings with reducers for 3/4" and 1/2" conduit



Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Agency Certification	
UL	E117594
General	
Product Family	Power Distribution
Series	130128
Enclosure Rating	NEMA 4X
GFCI Reset	N/A
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	Watertite® Wet-Location Wiring Solutions
Product Name	Watertite®
Receptacle Type	N/A
Type	FD Box - Industrial Duty
UPC	78172542282
Woodhead	Yes
Physical	
Cord Diameter	N/A
Cord Grip Body Size	N/A
Cord Length	N/A
Feed-Thru	No
Flip Lid	No
Material - Housing	PVC
Net Weight	1542.212/g
Number of Receptacles	0
Packaging Type	Carton
Electrical	
Cord Type	N/A
Current - Maximum per Contact	N/A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	N/A
Voltage - Maximum	N/A
Material Info	
Engineering Number	455-FD3
Reference - Drawing Numbers	
Sales Drawing	SD-130128-003

EU ELV
Not Relevant

EU RoHS
Compliant with
Exemption 6(c)
REACH SVHC
Not Contained Per -
ED/30/2017 (7 July
2017)
Halogen-Free
Status
Not Low-Halogen
Need more information on product
environmental compliance?

China RoHS

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

130128 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION