

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200310006](#)
Status: **Active**
Overview: [Brad® Nano-Change® (M8) Products](#)
Description: Nano-Change® (M8) Receptacle, 4 Poles, M8 x 0.5 Mounting Threads, Male (Straight) to 22 AWG Leads, 0.30m (11.81") Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family Industrial Receptacles
 Series [120031](#)
 IP Rating IP67
 NEMA Rating NEMA 6
 Overview [Brad® Nano-Change® (M8) Products](#)
 Product Name Nano-Change® (M8)
 Type Single Ended (pigtail)
 UPC 883906177782

Physical

Coupling Type External Thread
 Gender Male
 Keyway None
 Length 0.30m
 Material - Component Nickel-plated Brass
 Mounting Thread Size M8 x 0.5
 Orientation Straight
 Panel Mount Front
 Poles 4
 Temperature Range - Operating -25°C to +90°C
 Wire Size AWG 24
 Wire/Cable Type Leads

Electrical

Current - Maximum per Contact 3.0A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 4R4F06E02C3003

Reference - Drawing Numbers

Sales Drawing SD-120090-027

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per -ED/01/2017 (12 January 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

| | |
|-----------------|-----------------|
| China ROHS | 50 Image |
| ELV | Not Relevant |
| RoHS Phthalates | Contained: DEHP |

Search Parts in this Series

[120031](#) Series