

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301880034](#)  
**Status:** **Active**  
**Overview:** Brad® Mini-Change® Connectors  
**Description:** Mini-Change® (M12) 5 Pole, Female Receptacle, PCB Mount, 0.0278m (1.094") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Receptacles
Series	<a href="#">130188</a>
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	<a href="#">Brad® Mini-Change® Connectors</a>
Product Name	Mini-Change®
Type	Single Ended (pigtail)
UPC	78678833195

**Physical**

Coupling Type	Internal Thread
Gender	Female
Keyway	Single
Length	0.0278m
Material - Component	Nickel-plated Brass
Mounting Thread Size	1/2" - 14 NPT
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	N/A

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

**Material Info**

Old Part Number	67-0075
-----------------	---------

**Reference - Drawing Numbers**

Sales Drawing	SD-130188-002
---------------	---------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[130188 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**