

Part Number: [1200659527](#)
Status: Active
Overview: [Brad® M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable \(European Market\)](#)
Description: Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 5 Poles, Male (Straight) to Pigtail, 22 AWG, Unshielded WSOR Cable, Grey 5th Wire, 2.0m (6.56') Length

Documents:

[도면 \(PDF\)](#) [RoHS 증명서\(PDF\)](#)

Agency Certification

UL	E152210
일반적 특성	
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
IP Rating	IP67
원료 - 컨택부	황동
전체보기	Brad® M8 and M12 Cordsets with Knurled Hexnuts and WSOR Cable (European Market)
제품명	Micro-Change® (M12)
프로토콜	N/A
Region	유럽
타입	Single Ended
UPC	889056070706
물리적 특성	
케이블 지름	5.50mm (.216")
케이블 길이	2.0m (6.56')
색상 - 케이블 외피	Black
커플링 스타일	Knurled Hexnut, 나사산
암수구분	숫나사 - 피그테일
Keyway	싱글
LED 표시기	No
원료 - 케이블 외피	TPU
원료 - 커넥터 본체	TPU
원료 - 연결 Nut	Nickel-plated Brass
원재료 - 도금부	금
Net Weight	105.126/g
방향성	Straight to Pigtail
Poles	5
사용온도 범위	-25°C to +85°C
와이어 사이즈 (AWG)	22
와이어/케이블 타입	WSOR
전기적 특성	
전류 - 접촉 당 최대 출력	4.0A
최대전압	60V
원재료 정보	
Engineering Number	805006B30M020
참고 - 도면번호	
도면	1200659964-00P, SD-120065-073



EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/30/2017 (7 July 2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Relevant

Search Parts in this Series
[120065 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION