

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200650053](#)
Status: **Active**
Description: Micro-Push (M12) Single-Ended Cordset, 4 Poles, Female (Straight)-to-Pigtail, 22 AWG, Unshielded PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E152210

General

Product Family	Industrial Cordsets
Series	120065
Connector End A	Micro-Push (M12)
Connector End B	Pigtail
IP Rating	IP65
Material - Contact	Copper Alloy
Product Name	Micro-Push®
Protocol	N/A
Type	Single Ended
UPC	78678850599

Physical

Cable Diameter	4.70mm (.185")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	A-coded
Material - Cable Jacket	PVC
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25°C to +105°C
Wire Size AWG	22
Wire/Cable Type	Unshielded PVC

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Material Info

Engineering Number N04000A41M020G

Reference - Drawing Numbers

Sales Drawing SD-120065-084



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[120065](#) Series

Mates With

Micro-Change M12 Connectors