

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390216](#)
Status: **Active**
Overview: Brad® Mini-Change® Connectors
Description: Micro-Change (M12) to Mini-Change Double-Ended Cordset, 5 Poles, Male (90°) to Female (90°), DeviceNet Cable Plus Drain, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E152210

General

Product Family Industrial Cordsets
 Series [130039](#)
 Connector End A Micro-Change (M12)
 Connector End B Mini-Change
 IP Rating IP67
 Material - Contact Brass
 Overview [Brad® Mini-Change® Connectors](#)
 Product Name Micro-Change® (M12), Mini-Change®
 Region Europe
 Type Double Ended
 UPC 78678840356

Physical

Cable Diameter 6.86mm (.270")
 Cable Length 1.0m (3.28')
 Color - Cable Jacket Gray
 Coupling Style Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PVC
 Material - Coupling Nut Die-Cast Zinc
 Material - Plating Mating Gold
 Orientation 90° to 90°
 Poles 5
 Temperature Range - Operating -20°C to +80°C
 Wire Size AWG 22
 Wire/Cable Type Shielded-Twisted Pair

Electrical


Current - Maximum per Contact 4.0A
 Voltage - Maximum 250V AC/DC

Material Info

Engineering Number DND93A-M010

Reference - Drawing Numbers

Sales Drawing SD-130039-025



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130039 Series](#)