

Home: >

Part Number: 120066-0327

Image not available

Status: Active - Custom
Series: [120066](#)
Category: Molex Parts
Old Part Number: 884030A34M100

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Go to [Part Detail](#)

Series image - Reference only

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: ELV and RoHS Compliant

China RoHS:

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

[Product Compliance Statement](#)

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[COLLAPSE ALL](#)

▼ **General**

Status	Active - Custom
Category	Molex Parts
Series	120066
UPC	78678837297

▼ **Agency Certification**

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR6837
-----	--------

▼ **Material Info**

Old Part Number	884030A34M100
-----------------	---------------

Molex Connectors

Wire-to-Board
Board-to-Board
Wire-to-Wire
Input/Output (IO)
FFC/FPC
Sockets

Other Products

Fiber Optic Products
Antennas
Industrial Automation
Membrane Switches
Copper Flex
PCB Assemblies
Woodhead Electrical
Solid State Lighting
Application Tooling

Resources

Contact Us
Catalog
Cross-Reference
Industries
Literature
Product Name

Company Info

About Us
Careers
ecocare
Investors
Press Room
Shows & Events
Supplier Portal

Other Info

Feedback
Help
Legal Disclaimer
Trademarks
View Mobile Site
Privacy Policy
Sitemap

Stay Connected with Molex:

