

Home: >

Part Number: 130025-0099

Image not available

Status: Active - Custom
Series: [130025](#)
Category: Molex Parts
Old Part Number: DN11A-M210

[CHECK DISTRIBUTOR INVENTORY](#)

[Add to My Parts](#)

Go to [Part Detail](#)

Series image - Reference only

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU RoHS: RoHS Compliant by Exemption

China RoHS:

REACH SVHC: Not Reviewed

Low-Halogen Status: Not Reviewed

[Product Compliance Statement](#)

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Part Detail

[COLLAPSE ALL](#)

▼ **General**

Status	Active - Custom
Category	Molex Parts
Series	130025
UPC	78678849866

▼ **Agency Certification**

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

CSA	LR6837
UL	E152210

▼ **Material Info**

Old Part Number	DN11A-M210
-----------------	------------

Molex Connectors

Wire-to-Board
 Board-to-Board
 Wire-to-Wire
 Input/Output (IO)
 FFC/FPC
 Sockets

Other Products

Fiber Optic Products
 Antennas
 Industrial Automation
 Membrane Switches
 Copper Flex
 PCB Assemblies
 Woodhead Electrical
 Solid State Lighting
 Application Tooling

Resources

Contact Us
 Catalog
 Cross-Reference
 Industries
 Literature
 Product Name

Company Info

About Us
 Careers
 ecocare
 Investors
 Press Room
 Shows & Events
 Supplier Portal

Other Info

Feedback
 Help
 Legal Disclaimer
 Trademarks
 View Mobile Site
 Privacy Policy
 Sitemap

Stay Connected with Molex:

