

PRODUCTS
INDUSTRIES
CAPABILITIES
CAREERS
RESOURCES
Register Login
CONTACT MOLEX
FIND DISTRIBUTOR

Enter Part No. or Keyword  **Search**

Product Name Index
Cross Reference

Home: Cable Grips >

**Part Number: 130094-0280**

Standard Duty Support Grip, Locking Bale, Closed Mesh, Single Weave, Cable Diameter 44.45-50.55mm (1.750-1.990"), Approximate Break Strength 1428.82kg (3150 lbs)



Series image - Reference only

**Status:** Active  
**Series:** [130094](#)  
**Category:** Cable Grips  
**Overview:** [Support Grips](#)  
**EngineeringOldPN:** 35096

Go to **Part Detail** ▼

- REQUEST SAMPLES**
- CHECK DISTRIBUTOR INVENTORY**
- [Add to My Parts](#)
- [Email this page](#)

**Specifications & Other Documents:**

[Part Details \(PDF\)](#)

**Sales Drawings, 3D Models, and Brochures**

[Product Literature \(PDF\)](#)

Note - Please disable browser pop-up blockers to view documents on www.molex.com

**Product Environmental Compliance**

- EU ELV:** Not Reviewed
- EU RoHS:** Not Reviewed
- EU RoHS Phthalates:** Not Reviewed
- China RoHS:** Not Reviewed
- REACH SVHC:** Not Reviewed
- Low-Halogen Status:** Not Reviewed

- [EU RoHS Certificate of Compliance \(PDF\)](#)
- [Multiple Part Product Compliance Statements](#)  
EU RoHS, REACH SVHC, & Low-Halogen
- [Multiple Part Industry Compliance Documents](#)
  - \*IPC 1752A Class C
  - \*IPC 1752A Class D
  - \*Molex Product Compliance Declaration
  - \*IEC-62474
  - \*chemSHERPA (xml)

View Molex Environmental Position Statements: [Click here](#)

Request Molex's CMRT from [conflictminerals@molex.com](mailto:conflictminerals@molex.com)

**Part Detail**

**VIEW ALL**

▶ **General**

▶ **Physical**

▶ **Agency Certification**

▶ **Material Info**

**Application Tooling**

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application Tooling**

[Check our list of old tooling that used to be available for this part](#)



[Industries](#)

[Cross-Reference](#)

[Compliance](#)

[Koch Industries](#)

[ecocare](#)

[Investor Relations](#)

[Help](#)

[Literature](#)

[Jobs](#)

[Press Room / Press Releases](#)

[Legal | Trademarks](#)

[Sitemap](#)

[Supplier Portal](#)

[Terms & Conditions](#)

[Privacy Policy](#)

[Tradeshows](#)



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2019