

- ×
- [Products](#)
  - [Industry Solutions](#)
  - [CAREERS](#)
  - [Resources](#)
  - [Find Distributor](#)
  - [Contact Molex](#)

Enter Part No. or Keyw

 [Product Name Index](#)

 [Cross Reference](#)



## Part Number: 130144-0023

**Safeway Plug, 2 Pole/3 Wire, NEMA L5-15, 125V**



Series image - Reference only

**Status:** Active  
**Series:** [130144](#)  
**Category:** Wiring Devices  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Engineering/Old PN:** 4720

## Product Environmental Compliance

[EU ELV](#):Not Reviewed

[EU RoHS](#):Not Reviewed

[EU RoHS Phthalates](#):Not Reviewed

[China RoHS](#):Not Reviewed

[REACH SVHC](#):Not Reviewed

[Low-Halogen Status](#):Not Reviewed

## Part Detail

### General

<b>Status</b>	<b>Active</b>
<b>Category</b>	Wiring Devices
<b>Series</b>	<a href="#">130144</a>
<b>IP Rating</b>	N/A
<b>NEMA Configuration</b>	NEMA L5-15
<b>Overview</b>	<a href="#">Heavy-Duty Industrial Wiring Devices</a>
<b>Product Literature Order No</b>	987650-8068
<b>Product Name</b>	Safeway
<b>Receptacle Type</b>	N/A
<b>Specialty</b>	N/A
<b>Type</b>	Plug
<b>UPC</b>	78678870406

### Physical

<b>Flange</b>	No
<b>Flip Lid</b>	No
<b>Gender</b>	Male
<b>Length</b>	N/A
<b>Locking Blade</b>	Yes

**Poles** 2-pole/3-wire  
**Electrical**

---

**(Please review the Product Specification for specific details.)**

<b>Cord Type</b>	N/A
<b>Current - Maximum per Contact</b>	15.0A
<b>GFCI</b>	No
<b>Lighted Connector</b>	No
<b>Voltage - Maximum</b>	125V
<b>Agency Certification</b>	

---

**Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)**

<b>CSA</b>	LR6837
<b>UL</b>	E10176

---

**Material Info**

**Engineering Number** 4720

---

## Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

---

### Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

---

#### Products+

- [Product Categories](#)
- [Product Index](#)
- [Industries](#)

#### Quick Links+

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Press Room / Press Releases](#)
- [Sitemap](#)
- [Terms & Conditions](#)

#### Resources+

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback | Help](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshows](#)

#### Stay Connected



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018