

- ×
- [Products](#)
 - [Industry Solutions](#)
 - [CAREERS](#)
 - [Resources](#)

- [Find Distributor](#)
- [Contact Molex](#)

Enter Part No. or Keyw

 [Product Name Index](#)

 [Cross Reference](#)



Part Number: 130149-0027

Safeway Flanged Inlet with Locking Blade, 2 Pole/3 Wire, NEMA L5-20, 125V



Series image - Reference only

Status: Active

Series: [130149](#)

Category: Wiring Devices

Overview: [Heavy-Duty Industrial Wiring Devices](#)

Engineering/Old PN: 2647MB

Product Environmental Compliance

[EU ELV](#):Not Reviewed

[EU RoHS](#):Not Reviewed

[EU RoHS Phthalates](#):Not Reviewed

[China RoHS](#):Not Reviewed

[REACH SVHC](#):Not Reviewed

[Low-Halogen Status](#):Not Reviewed

Part Detail

General

| | |
|------------------------------------|--|
| Status | Active |
| Category | Wiring Devices |
| Series | 130149 |
| IP Rating | N/A |
| NEMA Configuration | NEMA L5-20 |
| Overview | Heavy-Duty Industrial Wiring Devices |
| Product Literature Order No | 987650-8068 |
| Product Name | Safeway |
| Receptacle Type | Single |
| Specialty | N/A |
| Type | Inlet |
| UPC | 78678802647 |

Physical

| | |
|----------------------|------|
| Flange | Yes |
| Flip Lid | No |
| Gender | Male |
| Length | N/A |
| Locking Blade | Yes |

Poles 2-pole/3-wire
Electrical

(Please review the Product Specification for specific details.)

| | |
|--------------------------------------|-------|
| Cord Type | N/A |
| Current - Maximum per Contact | 20.0A |
| GFCI | No |
| Lighted Connector | No |
| Voltage - Maximum | 125V |
| Agency Certification | |

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

| | |
|------------|--------|
| CSA | LR6837 |
| UL | E10176 |

Material Info

Engineering Number 2647MB

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products+

- [Product Categories](#)
- [Product Index](#)
- [Industries](#)

Quick Links+

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Press Room / Press Releases](#)
- [Sitemap](#)
- [Terms & Conditions](#)

Resources+

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback | Help](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshows](#)

Stay Connected



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018