

- ×
- [Products](#)
 - [Industry Solutions](#)
 - [CAREERS](#)
 - [Resources](#)
 - [Find Distributor](#)
 - [Contact Molex](#)

Enter Part No. or Keyw

 [Product Name Index](#)

 [Cross Reference](#)



Part Number: 130150-0038

20 Amp Watertite Pin and Sleeve Connector with Flip Lid, 2 Pole/3 Wire, 277V, Gray



Series image - Reference only

Status: Active

Series: [130150](#)

Category: Wiring Devices

Overview: [Watertite® Wet-Location Wiring Solutions](#)

Engineering/Old PN: 320C5

Product Environmental Compliance

[EU ELV](#):Not Reviewed

[EU RoHS](#):Not Reviewed

[EU RoHS Phthalates](#):Not Reviewed

[China RoHS](#):Not Reviewed

[REACH SVHC](#):Not Reviewed

[Low-Halogen Status](#):Not Reviewed

Part Detail

General

Status	Active
Category	Wiring Devices
Series	130150
Comments	IEC Configuration 309-1/309-2
IP Rating	IP67
NEMA Configuration	N/A
Overview	Watertite® Wet-Location Wiring Solutions
Product Name	Watertite
Receptacle Type	Single
Specialty	Pin and Sleeve
Type	Connector
UPC	78678862200

Physical

Flange	No
Flip Lid	Yes
Gender	Female
Length	241.30mm (9.500")
Locking Blade	No

Poles 2-pole/3-wire
Electrical

(Please review the Product Specification for specific details.)

Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	277V

Engineering Number 320C5

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

Products+

- [Product Categories](#)
- [Product Index](#)
- [Industries](#)

Quick Links+

- [Company Information](#)
- [Contact Molex](#)
- [Cross-Reference](#)
- [Koch Industries](#)
- [Investor Relations](#)
- [Literature](#)
- [Press Room / Press Releases](#)
- [Sitemap](#)
- [Terms & Conditions](#)

Resources+

- [Supply Chain Transparency](#)
- [Business Continuity](#)
- [Compliance](#)
- [ecocare](#)
- [Feedback | Help](#)
- [Jobs](#)
- [Legal | Trademarks](#)
- [Supplier Portal](#)
- [Privacy Policy](#)
- [Tradeshows](#)

Stay Connected



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2018