




CABLE LENGTH TOLERANCES				
<.3M [1FT]: +19mm-0 [+.75in-0]				
.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]				
.9 - 1.8M [3 - 6FT]: +55.6mm-0 [+2.19in-0]				
1.8 - 3.7M [6 - 12FT]: +88.9mm-0 [+3.50in-0]				
3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]				
7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]				
14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]				
OVER 30M [100FT] +2% OF FINISHED LENGTH				

PART NUMBER LEGEND

703000D02F1201

(B1)

POLE COUNT:
(2-6 POLES)

CABLE TYPE
22AWG SHLD, PVC

COUPLING NUT OPTIONS
BLANK= DIE CAST ZINC
1= 303 STAINLESS STEEL
2= NON METALLIC
8= 316 ST. STEEL

FINISHED LENGTH:
F010= 1 FOOT
F100= 10 FEET

M005= 0.5 METER
M010= 1 METER
M100= 10 METER

- NOTES:
1. MATERIAL: AS NOTED

2. FINISH: AS NOTED

3. ELECTRICAL:

VOLTAGE: 250V AC/DC

CURRENT: 4A

4. TEMP RATING: -20°TO +105°C

5. PROTECTION: IP67 (WHEN MATED)

6. COUPLING THREAD: 1/2-20 UNF

7. UL LISTED FILE: E152210 (B1)

CSA CERTIFIED FILE: LR6837

8. ALL DIMENSIONS ARE FOR REFERENCE
UNLESS TOLERANCED OR NOTED OTHERWISE

9	WRAP LABEL	VINYL	YELLOW
8	OVERMOLD	TPC	YELLOW
7	O-RING	NITRILE	RED
6	COUPLING NUT, FEMALE THD (-2 OPT)	DELRIN	WHITE
5	COUPLING NUT, FEMALE THD (-1 & -8 OPT)	ST. STEEL	PASSIVATED
4	COUPLING NUT, FEMALE THD (STD OPT)	ZINC DIE CAST	BLACK
3	CONTACT SOCKET	COPPER ALLOY	GOLD PLATED
2	FEMALE INSERT	NYLON	BLACK
1	CABLE, 22 AWG, SHIELDED	PVC JACKET	YELLOW
ITEM	DESCRIPTION	MATERIAL	FINISH

DOCUMENT STATUS	P1	RELEASE DATE	2024/08/21	17:05:16
-----------------	----	--------------	------------	----------

