Part Number : 1200790276
Product Description : M12 Signal, A-Coded, M12 Push-Pull Ultra-Lock Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 0.34mm² (22 AWG), Black PVC Cable, 10.0m (32.81') Length
Series Number : 120079
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : W05006E03M100

Documents and Resources

Drawings

1200790276_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120079
Description	M12 Signal, A-Coded, M12 Push-Pull Ultra-Lock Single-Ended Cordset, 5 Poles, Male (Straight) to Pigtail, 0.34mm² (22 AWG), Black PVC Cable, 10.0m (32.81') Length
IP Rating	IP67, IP69K
Product Name	M12 Signal Push-Pull,Ultra-Lock (M12)
Type	Single Ended
UPC	78172507829

Agency

CSA	LR6837

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.80mm (.230")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Black

Connector End A	M12 Signal Push-Pull
Connector End B	Pigtail
Coupling Style	Push-Pull
Gender	Male-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Stainless Steel
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	1451.000/g
Orientation	Straight to Pigtail
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	22