



Part Number : [1200800035](#)

Product Description : Ultra-Lock (M12) to Micro-Change (M12) In-Line Splitter, 4 Pole, 3-Female (Straight) to 4-Male (Straight), 0.34mm² PUR/PVC Cable, 0.30m Length

Series Number : 120080

Status : Obsolete

Product Category : Industrial Tees and Splitters

Engineering Part Number : 8W4A30A09M010

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Industrial Tees and Splitters
Series	120080
Description	Ultra-Lock (M12) to Micro-Change (M12) In-Line Splitter, 4 Pole, 3-Female (Straight) to 4-Male (Straight), 0.34mm ² PUR/PVC Cable, 0.30m Length
IP Rating	IP69K
Product Name	Ultra-Lock (M12)
Type	Splitter - In-line
UPC	78678887357

Agency

CSA	LR6837
-----	--------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Ultra-Lock (M12)
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	1.0m
Leg 2 Length	1.0m
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Nickel-plated Brass
Poles	3 Female/4 Male

Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-30°C to +90°C

This document was generated on Feb 26, 2026

Obsolete