

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201080373](#)
Status: **Active**
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, TPE Cable, 2.0m (6.56') Length, 6.99mm (.275") Diameter, Teal
Replacement Part Number : <http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=13004800961300480096> (drop-in)

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E361772
General	
Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Performance Category	5e
Product Name	Micro-Change (M12)
Protocol	EtherNet
Replacement Part Number	1300480096 (drop-in)
Type	Double Ended
UPC	78172543345
Physical	
Cable Diameter	6.99mm (.275")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +75°C
Wire Size AWG	24
Wire/Cable Type	TPE
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	30V
Material Info	
Engineering Number	E11A06007M020
Reference - Drawing Numbers	
Sales Drawing	SD-120108-057

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120108](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION