

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300070176

Status:


Active

Overview:

Brad Mini-Change Connectors

Description:

Mini-Change Single-Ended Straight Cordset, 8 Poles, B-Size Micro, Female (Straight) to Pigtail, 22 AWG, PVC Cable, 5.0m (16.40') Length



Series image - Reference only

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
General	
Product Family	Industrial Cordsets
Series	130007
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Mini-Change Connectors
Product Name	Mini-Change
Protocol	DeviceNet
Region	America
Type	Single Ended
UPC	78678844515
Physical	
Cable Diameter	6.10mm (.240")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-20° to +75°C
Wire Size AWG	22
Wire/Cable Type	STOOW
Electrical	
Current - Maximum per Contact	2.5A
Voltage - Maximum	600V
Material Info	
Engineering Number	208000A04M050
Reference - Drawing Numbers	
Sales Drawing	SD-130007-007-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130007 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION