
Part Number : 1300080312
Product Description : Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 22-18 AWG, PVC Cable, 5.0m (16.40') Length
Series Number : 130008
Status : Not Recommended For New Design
Product Category : Circular Industrial Cordsets
Engineering Part Number : 303001B20M050



Documents and Resources

Drawings

1300080312_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	Circular Industrial Cordsets
Series	130008
Description	Mini-Change C-Size Single-Ended Cordset, 19 Poles, Female (90°) to Pigtail, 22-18 AWG, PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Mini-Change
Protocol	DeviceNet
Type	Single Ended
UPC	78678898820

Electrical

Current - Maximum per Contact	2.0A, 3.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	11.43mm (.450")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Black Epoxy Coated Zinc

Material - Plating Mating	Gold
Net Weight	985.440/g
Orientation	90° to Pigtail
Poles	19
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	18, 22