



Part Number : [1300250048](#)

Product Description : Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18/15 AWG, DeviceNet Thick (Trunk) Cable, 0.305m (1.0') Length

Series Number : 130025

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Number : DN11A-M003

Documents & Resources

Drawings

[1300250048_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130025
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 18/15 AWG, DeviceNet Thick (Trunk) Cable, 0.305m (1.0') Length
IP Rating	IP67
Product Name	DeviceNet Trunk,Mini-Change
Type	Double Ended
UPC	78678847701

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	300V AC/DC

Physical

Cable Diameter	12.10mm (.480")
Cable Length	0.30m (11.81")
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None

Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Zinc Die-Cast
Material - Plating Mating	Gold
Net Weight	97.470/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	Thick (Trunk)
Wire Size (AWG)	15, 18