



Part Number : [1300830773](#)

Product Description : Woodhead POW-R-MITE
Industrial Duty Cable Reel, 16/3 SOW, 15.24m (50.0')
Cord Length with 30W Maximum Incandescent Spot
Light and Ball Stop

Series Number : 130083

Status : Active

Product Category : Electrical Reels

Engineering Number : 9228-1610S



Documents & Resources

Drawings

[1300830773_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Electrical Reels
Series	130083
Description	Woodhead POW-R-MITE Industrial Duty Cable Reel, 16/3 SOW, 15.24m (50.0') Cord Length with 30W Maximum Incandescent Spot Light and Ball Stop
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678834992

Electrical

Current - Maximum per Contact	9.0A
GFCI	No
Lamp Wattage - Maximum	30W
On/Off Switch	Yes
Transformer Type	Reel Mounted
Voltage - Maximum	120V

Physical

Bulb Included	Yes
Cable Length	N/A
Cable Movement	Ratchet Lock
Cord Length	15.24m (50.0')
Cord Type	16/3 SOW

Depth	0.34m (13.50")
Drum Lock	Ratchet
Duty	Industrial
Guide Arm	5° increments over 270° Arc
Height	0.37m (14.50")
Lamp Type	Incandescent
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Width	244.35mm (9.620")
Wire Size (AWG)	16