
molex



Part Number : 1300920166
Product Description : Aero-Motive Self-Contained Slip Ring, 21A, 12 AWG, 28 Conductors, Bore Size 38.10mm (1.500") Diameter
Series Number : 130092
Status : Active
Product Category : Slip Rings
Engineering Part Number : SR328

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)6375-DC (05 Nov 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Slip Rings
Series	130092
Description	Aero-Motive Self-Contained Slip Ring, 21A, 12 AWG, 28 Conductors, Bore Size 38.10mm (1.500") Diameter
Component Type	Self-Contained
Product Name	Aero-Motive
UPC	78678867808

Agency

CSA	LR29921

Electrical

Current - Maximum per Contact	21.0A
Voltage - Maximum	600V

Physical

Center Bore Diameter	38.10mm (1.500")
Mounting Style	Horizontal
Net Weight	1.000/g
Number of Conductors	28
Packaging Type	Carton
Speed (RPM)	Continuous 125
Temperature Range - Operating	-40°C to +120°C
Wire Size (AWG)	12