



Part Number : [1300940317](#)


Product Description : Standard Duty Support Grip, Single Eye, Split Lace, Single Weave, Cable Diameter 25.40-31.50mm (1.000-1.240"), Approximate Break Strength 762.04kg (1680 lbs), Stainless Steel

Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 35168SS



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Standard Duty Support Grip, Single Eye, Split Lace, Single Weave, Cable Diameter 25.40-31.50mm (1.000-1.240"), Approximate Break Strength 762.04kg (1680 lbs), Stainless Steel
NEMA Rating	NEMA 4
Product Name	Standard Duty
Type	Support Grip
UPC	78678809824

Physical

Approximate Break Strength	762.04kg (1680 lbs)
Bale Length	0.229m (9.00")
Body Style	Straight
Cable Diameter	25.40-31.50mm (1.000-1.240")
Color - Grommet	N/A
Eye Type	Single
Gender	N/A
Material - Body	N/A
Material - Grip	Stainless Steel
Mesh Length	0.38m (15.00")
Number of Holes	N/A
O-Ring	No
Thread Size	N/A