Part Number : 1300950135
Product Description : Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.813m (32.00"), Approximate Break Strength 4354.49kg (9600 lbs)
Series Number : 130095
Status : Active
Product Category : Cable Grips
Engineering Number : 35880



Documents & Resources

Drawings

1300950135_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130095
Description	Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.813m (32.00"), Approximate Break Strength 4354.49kg (9600 lbs)
Product Name	Heavy Duty
Type	Pulling Grip
UPC	78678835880

Agency

CSA	LR32159

Physical

Approximate Break Strength	4354.49kg (9600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Diameter	1"
Eye Type	Rotating
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.813m (32.00")
Number of Holes	N/A
O-Ring	N/A

Thread Size	N/A