



Image coming soon

Part Number : [1301230081](#)
Product Description : I-Beam Festoon Intermediate Car Round S6
Series Number : 130123
Status : Active
Product Category : Festoons
Engineering Part Number : 0639611

Documents and Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Festoons
Series	130123
Description	I-Beam Festoon Intermediate Car Round S6
Component Type	Car - Intermediate
Product Name	Aero-Motive
Type	I-Beam
UPC	78678863099

Physical

Beam Size	S6 - 152.40mm
Cable Height - Maximum	26.16mm (1.030")
Combined Cable Weight-Max./Car	79.38kg (175.0 lb)
Depth	209.55mm (8.250")
Duty	Heavy
Height	336.55mm (13.250")
Length	325.88mm (12.830")
Material - Coating	Powder Coating
Material - Metal	Steel
Material - Wheel	Polyurethane
Number of Cars	1
Packaging Type	Individual Carton
Saddle Radius	112.78mm (4.440")
Thread Size	N/A
Travel Speed - Maximum	121.92 mpm (400 fpm)
Wire/Cable Type	Round