

6


5

4


3

2


1

FEMALE INSERT
FACE VIEW

1 DRAIN WIRE
2 WHITE<DB>
3 YELLOW<DG>
4 BLUE <DA>

MALE INSERT
FACE VIEW

1 DRAIN WIRE
2 WHITE<DB>
3 YELLOW<DG>
4 BLUE <DA>



CC33A-J30-M020

Wire type
20/3C AWG Brown
PVC

cable length
M020----2 Meter
M100-----10 Meter

MECHANICAL
CONTACT: GOLD/NICKEL OVER COPPER ALLOY
INSERT : NYLON 6/6
O-RING: RED VITON
COUPLING NUT: ZINC DIECAST WITH BLACK EPOXY COATED
MOLDED BODY: GREY PVC
CABLE COLOR: BROWN
CABLE MARKING: FANC-110SBH KURAMO FA(JAPANESE WORDS)
CC-LINK Ver.1.10 KURAMO E162205-K c  us AWM Style 2464
I A 80C 300V VW-1 FT1 LF

ELECTRICAL
VOLTAGE RATING: 250V AC/DC
AMPERAGE: 4A

ENVIRONMENTAL
PROTECTION: IP67 PER IEC 60529
IP68 PER SPEC PS-120001-001
OPERATION TEMP: 0°C~80°C

CABLE MARKING UPDATE EC NO: IGC2015-1192 DRWN: CAAVILES 2014/12/30 CHKD: TWOLDEGE APPR: JFMURPHY 2012/11/01				QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE INCH/MM				SCALE 1:1		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
DESCRIPTION <																		