**Part Number :** 1300980225
**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437")
**Series Number :** 130098
**Status :** Active
**Product Category :** Cable Grips
**Engineering Part Number :** 5624



## Documents and Resources

### Drawings

1300980225_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| China RoHS | Not Reviewed |
| EU ELV | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC | Not Reviewed |
| EU RoHS | Not Reviewed |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Cable Grips |
| Series | 130098 |
| Description | MAX-LOC Strain Relief Cord-Sealing Grip, 3/4" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437") |
| NEMA Rating | NEMA 3R |
| Product Name | MAX-LOC |
| Type | Strain Relief Grip |
| UPC | 78678872210 |

### Agency

| | |
|---|---|
| CSA | LR32159 |
| UL | E76954 |

### Physical

| | |
|---|---|
| Approximate Break Strength | N/A |
| Bale Length | N/A |
| Body Style | Straight |
| Cable Diameter | 9.53-11.10mm (.375-.437") |
| Color - Grommet | Green |
| Eye Type | N/A |
| Gender | Male |
| Material - Body | Nylon |
| Material - Grip | N/A |
| Mesh Length | N/A |
| Number of Holes | 1 |
| O-Ring | No |
| Thread Size | 3/4" NPT |

## Mates With / Use With

**Use with Part(s)**

| Description | Part Number |
| --- | --- |
| MAX-LOC Lock Nut 3/4" NPT | 1300990144 |
| MAX-LOC Gasket Sealing Ring, 3/4" NPT, Black | 1300990150 |
| MAX-LOC O-Ring, 3/4" NPT | 1301800333 |