



Part Number : [847020009](#)
Product Description : Receptacle, RJ-45 Punchdown with 100 Ohm Resistors, Panel Mount Receptacle Jack
Series Number : 84702
Status : Obsolete
Product Category : Circular Industrial Connectors



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Product not active
China RoHS	Product not active
EU ELV	Product not active
Low-Halogen Status	Product not active
REACH SVHC	Product not active
EU RoHS	Product not active

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Circular Industrial Connectors
Series	84702
Description	Receptacle, RJ-45 Punchdown with 100 Ohm Resistors, Panel Mount Receptacle Jack
IP Rating	IP67
Product Name	RJ45
Type	110 Punchdown
UPC	883906429300

Electrical

Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Physical

Coupling Type	External Thread
Gender	Male
Keyway	None
Length	N/A
Material - Component	ABS
Mounting Thread Size	1" - 14 UNC
Orientation	Straight
Panel Mount	Front
Poles	N/A
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	N/A
Wire Size (AWG)	N/A