



Part Number : [1300830238](#)

Product Description : Woodhead POW-R-MITE
Industrial Duty Cable Reel, 10/6 SOW, 6.10m (20.0')
Cord Length

Series Number : 130083

Status : Active

Product Category : Electrical Reels

Engineering Part Number : 92464



Documents and Resources

Drawings

[1300830238 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Electrical Reels
Series	130083
Description	Woodhead POW-R-MITE Industrial Duty Cable Reel, 10/6 SOW, 6.10m (20.0') Cord Length
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Enclosure Rating	NEMA 4
NEMA Configuration	N/A
Product Name	POW-R-MITE
Type	Cable Reel
UPC	78678879235

Agency

CSA	LR29921
UL	E22769

Electrical

Current - Maximum per Contact	14.0A
GFCI	No
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

Physical

Bulb Included	N/A
Cable Length	N/A
Cable Movement	Ratchet Lock
Cord Length	6.10m (20.0')
Cord Type	10/6 SOW

Depth	0.34m (13.50")
Drum Lock	Ratchet
Duty	Industrial
Guide Arm	5° increments over 270° Arc
Height	0.37m (14.50")
Lamp Type	N/A
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	6
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Width	274.83mm (10.820")
Wire Size (AWG)	10