



Part Number : [1300910049](#)

Product Description : Woodhead Standard Duty Reel, 14/3 SJTOW Cord, 13.72m (45.0') Cord Length with 100W Incandescent Hand Lamp and Rubber Handle

Series Number : 130091

Status : Active

Product Category : Electrical Reels

Engineering Part Number : 990-106US



Documents and Resources

Drawings

[1300910049_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Electrical Reels
Series	130091
Description	Woodhead Standard Duty Reel, 14/3 SJTOW Cord, 13.72m (45.0') Cord Length with 100W Incandescent Hand Lamp and Rubber Handle
Enclosure Rating	NEMA 1
NEMA Configuration	NEMA 5-15
Product Name	Super-Safeway
Type	Cord Reel
UPC	78678833621

Agency

UL	E22769
----	--------

Electrical

Current - Maximum per Contact	11.0A
GFCI	No
Lamp Wattage - Maximum	100W
On/Off Switch	Yes
Voltage - Maximum	120V

Physical

Bulb Included	No
Cable Length	0.457m (1.50')
Cable Movement	Ratchet Lock
Cord Length	13.72m (45.0')
Cord Type	14/3 SJTOW
Depth	0.30m (11.75")

Drum Lock	Ratchet
Duty	Standard
Guide Arm	2 - Position
Height	0.36m (14.25")
Lamp Type	Incandescent
Material - Coating	Powder Coating
Material - Housing	Steel/Polycarbonate
Mounting Style	Rigid
Number of Conductors	3
Number of Receptacles	1
Packaging Type	Carton
Primary Cord/Cable Entry	N/A
Retraction Weight	1.4kg (3.0 lb)
Width	196.85mm (7.750")
Wire Size (AWG)	14