
MALLORY Mallory Sonalert Products Inc.	Part # PK-12N40PE-XCLQ
Sales Outline Drawing	Revision A

May not be suitable for all Medical and Aerospace applications.
Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz)	4000 ± 200
Operating Voltage (Vdc)	3 ~ 15
Rated Voltage (Vdc)	12
Current Consumption Max. (mA)	10 at Rated Voltage
Sound Pressure Level Min. (dB)	83 at 10cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +100
Storage Temperature (°C)	-30 ~ +110
Housing	PBT plastic resin (Color: Black)
Leading Pins	Tin Plated Brass
Weight (Grams)	1.0
Condition by wave (°C)	260 ± 5 / within 5 sec
Condition by hand (°C)	350 ± 20 / within 5 sec
Options	For other options contact factory

Dimensions: (units: mm) **ROHS Compliant**



4411 South High School Road, Indianapolis, Indiana 46241 USA ● Phone (317) 612-1000 ● Fax (317) 612-1010 ● http://www.mspindy.com