

Cable glands Progress® nickel-plated brass



Entry thread NPT

Type approval: Progress MS NPT

- Two-piece sealing insert
- not overall length insulated

Order number:	1000.1/2NPT
EAN:	7611614116754
Material	Nickel-plated brass
Seal	TPE
Operation temperature	-40°C / +100°C
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	NPT 1/2"
NEMA Type rating	4X
Clamping range with insert min.	8.0 mm
Clamping range with insert max.	11.0 mm
Clamping range without insert min.	11.0 mm
Clamping range without insert max.	15.0 mm
Wrench size	24 mm
Dimension H	23 mm
Thread length L	15 mm
UL - clamping range	10.6-11.0 mm
Dispatch	50