

Cable glands Progress® nickel-plated brass for high temperature application



Short entry thread metric

Type approval: Progress MS HT

- One-piece sealing insert
- not overall length insulated

Article no:	1000.12.91.065
E-No:	121079348
EAN:	7611614164656
Material	Nickel-plated brass
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M12x1.5
Clamping range min.	5.0 mm
Clamping range max.	6.5 mm
Wrench size	15 mm
Dimension H	17 mm
Thread length L	5 mm
Dispatch	50

1 = Metric coarse-pitch thread (with VDE test report)