


## Cable glands Progress® nickel-plated brass

**Short entry thread Pg****Type approval: Progress MS**

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1000.16.080</b>
E-No:	121075408
EAN:	7611614105765
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Entry thread	Pg 16
Clamping range min.	6.0 mm
Clamping range max.	8.0 mm
Wrench size	24 mm
Dimension H	23 mm
Thread length L	6.0 mm
UL - clamping range	8.0-8.0 mm
Dispatch	50

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.