

## Cable glands Progress® nickel-plated brass



### Short entry thread metric

#### Type approval: Progress MS

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1000.25.125</b>
E-No:	121079608
EAN:	7611614104348
Material	Nickel-plated brass
Seal	TPE / NBR
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Entry thread	M25x1.5
Clamping range min.	9.5 mm
Clamping range max.	12.5 mm
Wrench size	30 mm
Dimension H	25 mm
Thread length L	7 mm
UL - clamping range	10.4-12.5 mm
Dispatch	25

1 = Metric coarse-pitch thread (with VDE test report)

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.