

Cable glands Progress® nickel-plated brass



Entry thread NPT

Type approval: Progress MS NPT

- One-piece sealing insert
- not overall length insulated

Article no:	1000.2NPT.400
EAN:	7611614116716
Material	Nickel-plated brass
Seal	TPE
Operation temperature	-40°C / +100°C
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	NPT 2"
NEMA Type rating	4X
Clamping range min.	35.0 mm
Clamping range max.	40.0 mm
Wrench size	70 mm
Dimension H	37 mm
Thread length L	22 mm
UL - clamping range	35.0-40.0 mm
Dispatch	5