
Cable glands Progress® nickel-plated brass





Entry thread NPT

Type approval: Progress MS NPT

- One-piece sealing insert
- not overall length insulated

Article no:	**1000.3/4NPT.125**
EAN:	7611614116594
Material	Nickel-plated brass
Seal	TPE
Operation temperature	-40°C / +100°C
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	NPT 3/4"
NEMA Type rating	4X
Clamping range min.	9.5 mm
Clamping range max.	12.5 mm
Wrench size	30 mm
Dimension H	28 mm
Thread length L	15 mm
UL - clamping range	10.4-12.5 mm
Dispatch	25