

## Cable glands Progress® nickel-plated brass



### Short entry thread metric

#### Type approval: Progress MS

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1000.40.330</b>
E-No:	121079828
EAN:	7611614104423
Material	Nickel-plated brass
Seal	TPE / NBR
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Entry thread	M40x1.5
Clamping range min.	28.5 mm
Clamping range max.	33.0 mm
Wrench size	46 mm
Dimension H	31 mm
Thread length L	8 mm
UL - clamping range	29.5-32.8 mm
Dispatch	10

1 = Metric coarse-pitch thread (with VDE test report)

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.