


## Cable glands Progress® nickel-plated brass with antikink nozzle EPDM



### Short entry thread Pg

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1011.52</b>
E-No:	121230208
EAN:	7611614047751
Material	Nickel-plated brass
Seal	NBR
O-ring	NBR
Operation temperature	-40°C / +100°C
antikink nozzle	EPDM
Protection class	IP 68 / IP 69
Entry thread	Pg 11
Clamping range without insert min.	6.0 mm
Clamping range without insert max.	8.8 mm
Wrench size	20 mm
Dimension H	24 mm
Dimension T	45
Thread length L	6 mm
Dispatch	50