


Cable glands Progress® nickel-plated brass with antikink nozzle EPDM



Short entry thread metric

- One-piece sealing insert
- not overall length insulated

| | |
|------------------------------------|----------------------------|
| Order number: | 1017.52 |
| E-No: | 121231408 |
| EAN: | 7611614123998 |
| Material | Nickel-plated brass |
| Seal | NBR |
| O-ring | NBR |
| Operation temperature | -40°C / +100°C |
| antikink nozzle | EPDM |
| Strain relief | Version A acc. to EN 62444 |
| Protection class | IP 68 / IP 69 |
| Entry thread | M16x1.5 |
| Clamping range without insert min. | 6.0 mm |
| Clamping range without insert max. | 8.8 mm |
| Wrench size | 20 mm |
| Dimension H | 24 mm |
| Dimension T | 45 |
| Thread length L | 6 mm |
| Dispatch | 50 |

1 = Metric coarse-pitch thread (with VDE test report)