

Cable glands Syntec® nickel-plated brass with lamellar technology



Short entry thread metric

Type approval: SYNTEC MS

- One-piece sealing ring
- not overall length insulated

Article no:	1045.40.230
E-No:	121224508
EAN:	7611614230061
Material	Nickel-plated brass
Sealing ring	TPE
O-ring	NBR
Lamellar insert	Polyamide PA 6
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68
NEMA Type rating	4X
Entry thread	M40x1.5
Clamping range min.	15.0 mm
Clamping range max.	23.0 mm
Wrench size	46 mm
Dimension H	40 mm
Thread length L	8 mm
UL - clamping range	17.5-23.0 mm
Dispatch	10

Available on request:

- Entry thread Pg