

Cable glands Progress® nickel-plated brass with antikink spring



Short entry thread metric

Type approval: Progress MS FKN

- One-piece sealing insert
- overall length insulated

Order number:	1060.08.52.030
E-No:	121783108
EAN:	7611614195063
Material	Nickel-plated brass
Antikink spring	Stainless steel A2
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M8x1.25
Clamping range without insert min.	2.5 mm
Clamping range without insert max.	3.0 mm
Wrench size	11 mm
Dimension H	49 mm
Thread length L	5 mm
Note	1
Dispatch	10

1 = Metric coarse-pitch thread (with VDE test report)

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.

Available on request:

- Short entry thread with short one-piece or two-piece sealing insert.
- Long entry thread with short or full-length insulating one-piece or two-piece sealing insert.