

## Cable glands Progress® nickel-plated brass



### Short entry thread Pg

#### Type approval: Progress MS

- Two-piece sealing insert
- overall length insulated

<b>Order number:</b>	<b>1060.09</b>
E-No:	121063108
EAN:	7611614106472
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Entry thread	Pg 9
Clamping range with insert min.	6.0 mm
Clamping range with insert max.	8.0 mm
Clamping range without insert min.	8.0 mm
Clamping range without insert max.	10.5 mm
Wrench size	18 mm
Dimension H	22 mm
Thread length L	6.0 mm
UL - clamping range	7.1-8.0 mm
Dispatch	50

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.