

## Cable glands Progress® nickel-plated brass



### Short entry thread metric

#### Type approval: Progress MS

- Two-piece sealing insert
- overall length insulated

<b>Order number:</b>	<b>1060.17</b>
E-No:	121067408
EAN:	7611614105406
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Entry thread	M16x1.5
Clamping range with insert min.	6.0 mm
Clamping range with insert max.	8.0 mm
Clamping range without insert min.	8.0 mm
Clamping range without insert max.	10.5 mm
Wrench size	18 mm
Dimension H	22 mm
Thread length L	5 mm
UL - clamping range	7.1-8.0 mm
Dispatch	50



Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.