

Cable glands Progress® nickel-plated brass with antikink spring



Short entry thread metric

Type approval: Progress MS FKN

- Two-piece sealing insert
- overall length insulated

Order number:	1060.20.52
E-No:	121784508
EAN:	7611614195254
Material	Nickel-plated brass
Antikink spring	Stainless steel A2
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M20x1.5
Clamping range with insert min.	8.0 mm
Clamping range with insert max.	11.0 mm
Clamping range without insert min.	11.0 mm
Clamping range without insert max.	14.5 mm
Wrench size	24 mm
Dimension H	86 mm
Thread length L	6 mm
Dispatch	10

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.

Available on request:

- Short entry thread with short one-piece or two-piece sealing insert.
- Long entry thread with short or full-length insulating one-piece or two-piece sealing insert.