

## Cable glands Progress® nickel-plated brass



### Short entry thread metric

#### Type approval: Progress MS

- One-piece sealing insert
- overall length insulated

<b>Order number:</b>	<b>1060.32.255</b>
E-No:	121077718
EAN:	7611614105314
Material	Nickel-plated brass
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
NEMA Type rating	4X
Entry thread	M32x1.5
Clamping range min.	21.0 mm
Clamping range max.	25.5 mm
Wrench size	36 mm
Dimension H	28 mm
Thread length L	8 mm
UL - clamping range	22.2-25.5 mm
Dispatch	25

1 = Metric coarse-pitch thread (with VDE test report)

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.