

Cable glands Progress® stainless steel A2 for high temperature applications



Long entry thread Pg

- One-piece sealing insert
- not overall length insulated

Order number:	1100.09.96.105
EAN:	7611614134192
Material	CrNi stainless steel A2 (DIN EN 1.4305 / AISI 303)
Identification	1 groove
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	Pg 9
Clamping range without insert min.	8.0 mm
Clamping range without insert max.	10.5 mm
Wrench size	19 mm
Dimension H	20 mm
Thread length L	10 mm
Dispatch	50