

## Cable glands Progress® stainless steel A2



### Long entry thread metric

#### Type approval: Progress S2

- One-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1100.10.94.060</b>
E-No:	121623218
EAN:	7611614133560
Material	CrNi stainless steel A2 (DIN EN 1.4305 / AISI 303)
Identification	1 groove
Seal	TPE
O-ring	NBR
Operation temperature	-40°C / +100°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M10x1.5
Clamping range without insert min.	4.0 mm
Clamping range without insert max.	6.0 mm
Wrench size	13 mm
Dimension H	15 mm
Thread length L	10 mm
Note	1
Dispatch	50

1 = Metric coarse-pitch thread (with VDE test report)

Available with sealing inserts conformity with EN 45545 / NFPA 130. When placing an inquiry, prefix the article number by the capital F.