

## Cable glands Progress® stainless and acid-resistant steel A4 for high temper

**Long entry thread metric****Type approval: Progress S4 HT**

- Two-piece sealing insert
- not overall length insulated

<b>Order number:</b>	<b>1100.17.98</b>
E-No:	121604408
EAN:	7611614132822
Material	Stainless steel and acid resistant steel A4 CrNiMo (DIN EN 1.4435 / AISI 316L)
Identification	2 grooves
Seal	FPM
O-ring	FPM
Operation temperature	-40°C / +200°C
Strain relief	Version A acc. to EN 62444
Protection class	IP 68 (up to 10 bar) / IP 69
Entry thread	M16x1.5
Clamping range with insert min.	6.0 mm
Clamping range with insert max.	8.0 mm
Clamping range without insert min.	8.0 mm
Clamping range without insert max.	10.5 mm
Wrench size	19 mm
Dimension H	20 mm
Thread length L	10 mm
Dispatch	50